



Applications: Home & Corporate Offices
Libraries & Schools

Advantages:

- Portable Kit is Ideal for Remote Office Staff
- Hearing Loop Driver features Dual Action AGC for smooth, exceptional clarity of sound, volume thumb wheel, bass and treble controls and three inputs: dedicated, sensitive mic input, mic/line input and a line input
- System can drive audio to two loop fields at the same time: i.e. seat cushion, floor mat, chair pad.
- Blue LEDs indicate power connection on, signal source level and loop current.

Hearing Loop System for Computer Audio

This compact, seamless hearing loop system works with audio input from a computer, including “video chat” sessions, to improve clarity and comprehension. The personal-sized solution delivers clear sound to all brands of hearing aids, cochlear implants and telecoil receivers. Output options include the looped seat cushion, floor mat or chair pad. The audio field will accommodate people of any height while seated.



Specifications for System Components:

- Dimensions: 13” X 15” x 2” (seat cushion)
- Amplifier: IEC 60188-4 Compliant Driver
- Power: 110V AC
- Warranty: Three (3) Years



Looped Seat Cushion

Approximate Field Size



Compact Loop Driver (front and rear)



Audio Directions
@AudioDirections

1-833-234-4411
www.AD4H.com

Peggy Bell
(516) 697-0067
peggy@AD4H.com
(Southern States)

Sally Wood
(609) 240-7081
sally@AD4H.com
(Northern States)